


STERILE PRESATURATED DISPOSABLE HEAVY WEIGHT MICROFIBER MOPS

Designed for the Saturix[™] Hands-Free Mop Drop System



MA416S

Optimized Cleaning Performance with Convenience and Validated Sterility

Microfiber cleaning power coupled with our patented Hands-Free Mop Drop System provides consistent cleanliness and minimizes the spread of dirty cleaning solutions while improving productivity. A 70/30 IPA blend offers the perfect saturation level while our robust sterilization process offers absolute confidence.

Features and Benefits

- Removes 99.9% of particles down to .1 micron in size⁴
- 70% isopropyl alcohol (IPA), 30% DI water
- 305 ft² / 28 m² coverage per mop, 47% more than the leading competitor mops⁴
- Pocket mop design facilitates hands-free operation for ease of use and minimizes the spread of dirty cleaning solutions
- Ultra-high absorbency and coverage to maximize worker efficiency
- Consistent and even laydown
 of cleaning solutions
- Certificate of Sterility included



Visionary Cleaning System

Saturix is a complete system for critical cleaning featuring innovative carts, mops and wipes backed by 100 years of cleaning experience. With focused product selection, it's easy to find exactly what you need right now.

To learn more about our products, visit us online at **Saturix.com** or contact us at +1 (413) 598-8344 or info@saturix.com





Sterile Disposable Heavy Weight Microfiber Mops

Independently tested by a nationally renowned third party laboratory

Cleanroom Level Recommendation*

| Property | Typical Value |
|-------------------------|---|
| Face Material | 100% circular knit polyester microfiber, 290 gsm |
| Inner Layer Material | 3-layer, 100% non-woven polyester |
| Backing Material | 100% circular knit polyester |
| Weight (g) / Dry Weight | 68 g |
| Floor Coverage | 305 SqFt / 28 m ² |
| Absorbency | 252% |
| Application Usage | Floor, wall and ceiling cleaning for cleanrooms and other controlled environments |
| Shelf Life | 3 Years |
| Re-use | Disposable mop. Single use in cleanrooms, washable for reuse in grey areas |
| Chemical Resistance | Acids: non-effect, Alkali: non-effect |

Notes

- 1. Data shown are typical values and should not be used as product specifications.
- 2. Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions. Current and/or comparison data may be available. Please contact an FG Clean Wipes representative for details.
- 3. FG Clean Wipes makes general recommendations on which products are suitable for different cleanroom classifications. However, specific applications may affect that recommendation. The final decision should be made by the end user for their particular application.

4. Based on third party testing.

* Cleanroom class recommendations are based on typical industry-wide applications and general cleanliness classifications. Please consult our experienced FG Clean Wipes sales representatives for specific cleanroom selections for critical and/or specialized applications based on a wider selection of criteria.

To learn more about our products, visit us online at **Saturix.com** or contact us at +1 (413) 598-8344 or info@saturix.com.

