

MD216S

nformation Sheet

STERILE DISPOSABLE

# LIGHT WEIGHT MICROFIBER MOPS

Designed for the Saturix™ Hands-Free Mop Drop System

# Optimized Cleaning Performance and Efficiency with Validated Sterility

Microfiber cleaning power coupled with our patented Hands-Free Mop Drop System provides consistent cleanliness and minimizes the spread of dirty cleaning solutions while improving productivity. Our exacting sterilization process offers absolute confidence.



# Features and Benefits

- Removes 99.9% of particles down to .1 micron in size<sup>4</sup>
- 158 ft<sup>2</sup> / 14 m<sup>2</sup> coverage per mop
- Lightweight design is ideal for small area cleaning, reducing cleaning solution waste
- Pocket mop design facilitates hands-free operation for ease of use and minimizes the spread of dirty cleaning solutions
- Certificate of Sterility included

Item	Size	Quantity
MD216S	16" (40 cm mop system)	5 mops/bag • 20 bags/case



## Visionary Cleaning System

Saturix is a complete system for critical cleaning featuring innovative carts, mops and wipes backed by 100 years of cleaning experience. With focused product selection, it's easy to find exactly what you need right now.

To learn more about our products, visit us online at **Saturix.com** or contact us at +1 (413) 598-8344 or info@saturix.com





Sterile Disposable Light Weight Microfiber Mops

MD216S

Cleanroom Level Recommendation\*









		_	
1	4	0	
,	V	Ö	

Independently tested by a nationally renowned third party laboratory		
Property	Typical Value	
Face Material	100% circular knit polyester microfiber, 180 gsm	
Inner Layer Material	3-layer, 100% non-woven polyester	
Backing Material	100% circular knit polyester	
Weight (g) / Dry Weight	39 g	
Floor Coverage	158 SqFt / 14 m <sup>2</sup>	
Absorbency	335%	
Application Usage	Floor, wall and ceiling cleaning for cleanrooms and other controlled environments	
Shelf Life	3 Years	
Re-use	Disposable mop. Single use in cleanrooms, washable for reuse in grey areas	
Chemical Resistance	Acids: non-effect, Alkali: non-effect	

### Notes

- 1. Data shown are typical values and should not be used as product specifications.
- 2. Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions. Current and/or comparison data may be available. Please contact an FG Clean Wipes representative for details.
- 3. FG Clean Wipes makes general recommendations on which products are suitable for different cleanroom classifications. However, specific applications may affect that recommendation. The final decision should be made by the end user for their particular application.
- 4. Based on third party testing.

To learn more about our products, visit us online at Saturix.com or contact us at +1 (413) 598-8344 or info@saturix.com.



<sup>\*</sup> Cleanroom class recommendations are based on typical industry-wide applications and general cleanliness classifications. Please consult our experienced FG Clean Wipes sales representatives for specific cleanroom selections for critical and/or specialized applications based on a wider selection of criteria.